

Protect It! 3-Outlet Surge Protector, Direct Plug-In, 540 Joules, 3.4 A USB Charger, Diagnostic LED

MODEL NUMBER: SK30USB



Highlights

- 3 outlets/direct plug-in
- 540 joule rating
- 3.4 amp USB charging
- Diagnostic LED

Package Includes

- SK30USB surge suppressor

Description

The SK30USB surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 3 outlets and 540 joules of surge energy absorption. Diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. 3.4 amp USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 3 outlets / direct plug-in
- Surge suppression rating: 540 joules
- 3.4 amp USB Charger
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332180353
Product Type	Surge Protector
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	



Powering Business Worldwide

TRIPP LITE
SERIES

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green - Protected
CHARGING	
Number of Charging Ports	2
Total Charging Watts	10.5
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.1A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
EMI / RFI Filtering	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	6.30 x 2.70 x 4.00
Shipping Dimensions (hwd / cm)	16.00 x 6.86 x 10.16
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Dimensions (hwd / in.)	5.280 x 3.740 x 1.180
Unit Dimensions (hwd / cm)	13.40 x 9.50 x 3.00
Unit Weight (lbs.)	0.41
Unit Weight (kg)	0.19
Input Cord Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 42 (Canada); NOM (Mexico); UL 1449; UL 497A
Product Compliance	RoHS



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.