

# USB-A to RJ45 Serial Rollover Cable (M/M) - Cisco Compatible, 250 Kbps, 6 ft. (1.83 m), Gray

MODEL NUMBER: U209-006-RJ45-X



Connects your computer or laptop's USB port to your Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port.

## Features

**Connects Computer's USB Port to Cisco Device** Connect computer or laptop to Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port  
Works with older and new Cisco models  
6 ft. long

**Top-of-the-Line Performance** Supports data transfer rates up to 250 Kbps  
Supports remote wake-up and power management  
Utilizes FTDI chipset.

**Easy to Use** No other cables or adapters needed  
No external power required  
Driver CD included (drivers also available online for download if your computer has no CD drive)

## Highlights

- Supports data transfer rates up to 250 Kbps
- Supports remote wake-up and power management
- Compatible with Windows, Mac and Linux
- No cables, adapters or external power required

## System Requirements

- Computer with available USB port
- Cisco device with available RJ45 console port
- Windows, Mac or Linux operating system

## Package Includes

- U209-006-RJ45-X USB to RJ45 Cisco Serial Rollover Cable
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332190017
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Plating	Gold
PHYSICAL	
Color	Gray
Material of Construction	PVC
Cable Jacket Color	Gray



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Jacket Material	PVC
Cable Outer Diameter (OD)	2.5 mm
Wire Gauge (AWG)	26
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	1.20 x 4.70 x 4.10
Shipping Dimensions (hwd / cm)	3.05 x 11.94 x 10.41
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
Unit Packaging Type	Box
Unit Weight (lbs.)	0.2425
Unit Weight (kg)	0.11
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0-90% non-condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
Driver Required	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.