



- NOTES:**
1. Waterproof rate: IP67
 2. Gasket: EPDM Black
 3. Housing: ABS Black
 4. Screw: Brass
 5. O-ring: Silicone Clear
 6. Body: Nylon Black
 7. Sealing Nut: Nylon Black
 8. Connector: D-Sub 09Pin Male, in full gold plated
 9. Seals for Cable OD: $\phi 3.5\text{mm}-\phi 7.0\text{mm}$
 10. One Set Unassembled in One Zipper Bag

ROHS compliant
Unit: mm

Scale	Free	Customer-No.	
TOLERANCE		ASSMANN WSW-No.	A-DS09-HOOD-WP
UNIT	±0.5	Drawing-No.	ASS 6258 CO
DIM	TOL	Replace	rev01
Angle	TOL	Sheet	
Id.			
①	Cancel "A" logo&correct dimensions	03.04.2018	Amy
②	Drawn	22.04.2014	Joanna
Modification			
Date			
Name			

ASSMANN
components

1	2	3	4	5	6	7	A
1	2	3	4	5	6	7	A
1	2	3	4	5	6	7	B
1	2	3	4	5	6	7	C
1	2	3	4	5	6	7	D
1	2	3	4	5	6	7	E
1	2	3	4	5	6	7	F
1	2	3	4	5	6	7	G
1	2	3	4	5	6	7	H