Pushing Performance
Since 1945

Han S 450+_CC_RS_19.4 -20.6mm



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 2070
Specification	Han S 450+_CC_RS_19.4 -20.6mm
HARTING eCatalogue	https://harting.com/97000002070

Identification

Category	Accessories
Series of hoods/housings	Han® S
Description of hood/housing	Han® S 450 Plus
Type of accessory	Reduction seal insert

Technical characteristics

Clamping range	19.4 ... 20.6 mm

Material properties

Colour (accessories)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	66.73 g
Country of origin	China
European customs tariff number	85366990

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Commercial data

eCl@ss	27140807 Additional components cable gland
ETIM	EC003608
UNSPSC 24.0	39121431

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.