



Part Number : 190080031
Product Description : Flag Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm²) Wire, Metal Strip, Tab 6.35 x 0.81mm
Series Number : 19008
Status : Active
Product Category : Quick Disconnects
Engineering Number : BBZ-1159



Documents & Resources

Drawings
[190080031_sd.pdf](#)
[PK-19009-001-001.pdf](#)

3D Models and Design Files
[190080031_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19008
Description	Flag Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Metal Strip, Tab 6.35 x 0.81mm
Product Name	Krimptite
Type	Quick Disconnect
UPC	800755046694

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	0.611/g
Orientation	Flag
Packaging Type	Reel
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	Per Wire Specification
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator Rear Feed	<u>638027600</u>

This document was generated on Mar 12, 2025