





LOC	DIST	REVISIONS					
CM	52	TP	LTR	DESCRIPTION		DATE	OWN
			P	REV & REDWN PER EC 061B-0049-98		3-6-98	TB
							R5

1. ACCEPTS TERMINALS 61347-1 AND 350490-1.
2. RELAYS MAY BE MOUNTED ON 45.72 X 40.39 CENTERS.



RECOMMENDED CUT OUT
FOR 2.54 MAX THICK PANEL



2.54	.100	11.10	.437	32.26	1.270	—	—
1.52	.060	8.33	.328	32.00	1.260	45.72	1.800
0.38	.015	7.57	.298	31.62	1.245	40.39	1.590
0.25	.010	5.54	.218	29.72	1.170	35.43	1.395
0.13	.005	4.37	.172	14.61	.575	34.90	1.374
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

mm

0 PLC ±-

1 PLC ±-

2 PLC ±0.13

3 PLC ±-

4 PLC ±-

ANGLES ±-

MATERIAL NYLON, NATURAL

FINISH —

OWN T. BECK 3-6-98

CHK R. SWING 3-6-98

APP'D G. JONES 3-6-98

PRODUCT SPEC —

APPLICATION SPEC —

HEIGHT —

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

HOUSING, 11 CIRCUIT, KU TYPE,
RELAY CONNECTOR

SIZE A1 CAGE CODE 00779 DRAWING NO. 380993

RESTRICTED TO —

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV P