
**Part Number :** 190540097
**Product Description :** InsulKrimp Ring Tongue Terminal for 16-14 AWG,, Carton
**Series Number :** 19054
**Status :** Active
**Product Category :** Ring and Spade Terminals
**Engineering Part Number :** B-230-14HDX



## Documents and Resources

### Drawings

190540097_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-19902-009-001.pdf

PS-19902-013-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Ring and Spade Terminals |
| Series | 19054 |
| Description | InsulKrimp Ring Tongue Terminal for 16-14 AWG,, Carton |
| Comments | Heavy Duty |
| Keyword | Ring Terminal, Ring Terminals |
| Product Name | InsulKrimp |
| Style | Ring |
| Type | Ring Terminal, Metric Ring Terminal |
| UPC | 800753054769 |

### Agency

| | |
|---|---|
| CSA | LR18689 |
| UL | E32244 |

### Physical

| | |
|---|---|
| Barrel Type | Closed |
| Color - Resin | Yellow |
| Flammability | 94V-0 |
| Insulation | PVC |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Plating Mating | Tin |
| Net Weight | 2.836/g |
| Packaging Type | Carton |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Stud Size | 1/4" (M6) |
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter | 6.40mm max. |
| Wire Size (AWG) | 14, 16 |
| Wire Size $mm^2$ | 1.30-2.00 |

## Application Tooling

### Global

| Description | Part Number |
|---|---|
| PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5$mm^2$ (Rings, Spades, Hooks, Block Spades and Flanged Spades) | 640010100 |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool | 640160036 |



Downloaded from Arrow.com.