


© – TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M	PCN–25–266602	08AUG2026	GSK	CAS







FREE HANGING
(–2 ONLY)



PANEL CUTOUT
SCALE 1:1

OBSOLETE	#4–40 THREADED INSERTS	206486–6
	Ø.125 HOLES	206486–2
	Ø.125 HOLES	206486–1
	MOUNTING FEATURE	PART NUMBER

1. CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACES OF CONNECTOR.
2. WILL ACCEPT (9) SIZE 20 PIN CONTACTS.
3. MATERIALS:
   HOUSINGS: THERMOPLASTIC, BLACK
   THREADED INSERT: BRASS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± .005
4 PLC ± –
ANGLES ± –

MATERIAL 3

FINISH –

DWN A.STAUB BG 4/1/91
CHK W.G.LENKER 7–27–92
APVD K.BEAVER 7–27–92
PRODUCT SPEC 108–10024
APPLICATION SPEC —
WEIGHT

TE Connectivity

NAME
RECEPTACLE ASSEMBLY, STD SEX, SERIES 2, 11–9, CPC

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–206486	—

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV M

Downloaded from Arrow.com.