

## Internal SAS Cable, mini-SAS (SFF-8087) to 4-in-1 32pin (SFF-8484), 18-in. (0.5M)

MODEL NUMBER: **S510-18N**



### Highlights

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal Mini-SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths ( up to 6Gbps )
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution

### Package Includes

- 18in Internal SAS Cable, Mini-SAS SFF-8087 to SFF-8484

### Description

18" Internal Mini-SAS SFF-8087 to SFF-8484 controller to backplane cable. 30AWG, 8-pair cable with sideband signaling.

### Features

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal iPass assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths ( up to 6Gbps )
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution
- For controller to backplane applications

## Specifications

OVERVIEW	
UPC Code	037332143372
Technology	SAS; Ribbon/Internal
CONNECTIONS	
Side A - Connector 1	SFF-8087
Side B - Connector 1	SFF-8484
PHYSICAL	
Color	Black
Cable Length (ft.)	1.5



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Length (m)	0.46
Cable Length (in.)	18
Cable Length (cm)	45.72
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.