Part Number : 190430010
Product Description : Three Way Connector, Dual Male, Single Female Quick Disconnect Adapter, 6.35 x 0.81mm Tab Size, Non-Plated, Carton
Series Number : 19043
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : VWA-0



Documents and Resources

Drawings

190430010_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19043
Description	Three Way Connector, Dual Male, Single Female Quick Disconnect Adapter, 6.35 x 0.81mm Tab Size, Non-Plated, Carton
Product Name	Adapter
Style	Adapter
Type	Standard Quick Disconnect
UPC	800753050181

Electrical

Voltage - Maximum	N/A

Physical

Barrel Type	N/A
Gender	Dual
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Unplated

Downloaded from Arrow.com.

Material - Plating Termination	Unplated
Net Weight	1.132/g
Orientation	Straight
Packaging Type	Carton
Tab Thickness	0.81mm
Tab Width	6.35mm
Termination Interface Style	N/A
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

Downloaded from Arrow.com.