**Part Number :** 1200698597
**Product Description :** Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Shielded Black WSOR Cable, 1.0m (3.28') Length
**Series Number :** 120069
**Status :** Active
**Product Category :** Circular Industrial Cordsets
**Engineering Part Number :** 805S00BS1M010



## Documents and Resources

### Drawings

1200698597_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Circular Industrial Cordsets |
| Series | 120069 |
| Description | Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Shielded Black WSOR Cable, 1.0m (3.28') Length |
| IP Rating | IP67 |
| Product Name | Micro-Change (M12) |
| Protocol | N/A |
| Type | Single Ended |
| UPC | 889056131186 |

### Agency

| | |
|---|---|
| UL | E152210 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 60V |

### Physical

| | |
|---|---|
| Cable Diameter | 6.10mm (.240") |
| Cable Length | 1.0m (3.28') |
| Color - Cable Jacket | Black |
| Connector End A | Micro-Change (M12) |

Downloaded from Arrow.com.

| | |
|---|---|
| Connector End B | Pigtail |
| Coupling Style | Knurled Hexnut, Threaded |
| Gender | Female-Pigtail |
| Keyway | A-Coded |
| LED Indicator | None |
| Material - Cable Jacket | TPU |
| Material - Connector Body | TPU |
| Material - Contact | Brass |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - O-Ring | Fluoro-elastomer |
| Material - Plating Mating | Gold |
| Net Weight | 76.200/g |
| Orientation | Straight to Pigtail |
| Poles | 5 |
| Temperature Range - Operating | -25° to +85°C |
| Wire/Cable Type | UL 21215, Shielded TPU |
| Wire Size (AWG) | 22 |



Downloaded from Arrow.com.