

2014

RELEASED FOR PUBLICATION


THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT 2014 BY TE CONNECTIVITY

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-012854	08-20-14	DM	DM




4. THICKNESS: 3.18 [.125]

3. PART NO. 16-04477

2. TEMPERATURE RATING: -57°C TO +107°C [-70°F TO +225°F]

1. THIS PART IS USED ON HDP20 / HD30 SIZE 24 RECEPTACLES.

DIMENSIONS: MM [INCH]		DWN D. MEYER 20AUG2014	MATERIAL CLD CELL SPONGE	FINISH BLACK	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 0.76 [.030] 3 PLC ± 4 PLC ± ANGLES ± 5°		CHK I. GRANTCHARVORA 20AUG2014	 TE Connectivity		
		APVD D. MEYER 20AUG2014			
		PRODUCT SPEC	NAME GASKET, RECEPTACLE, SIZE 24 HDP20 / HD30 SERIES		
		APPLICATION SPEC	SIZE A 4	CAGE CODE 4AFU8	DRAWING NO C-16-04477
		WEIGHT .45 g	Customer Drawing		
		SCALE NONE	SHEET 1 OF 1	REV A	