All orders placed will be shipped out as usual, delivery times are expected to be affected due to COVID-19.Thank you for your continued support. Read More

Register to Get $10 Shipping Coupon



Metal DC Geared Motor - 6V 73RPM 2.5Kg.cm

SKU:FIT0495-E Brand:Other Reward Points: 99

* Model: 15RPM | 20RPM | 73RPM | 97RPM | 162RPM | 191RPM | 357RPM

Quantity: - +

ADD TO CART

Frequently Bought Together

Metal DC Geared Motor - 6V 73RPM 2.5Kg.cm + ... Controller (L298N) + Rome... Bluetooth 4.0 + Gravity: 2x2A ... Twin + Copper Cou... (4mm) =

You have choosen:0
Total amount:

BUY IT NOW

INTRODUCTION

This is a metal DC geared motor, 99:1 metal reducer. It has a small size and large torque. The maximum torque could arrive 2.5 kg.cm. It is stable and durable!

Romeo BLE Application connection - DFRobot

Metal DC Geared Motor - DFRobot dimension

SPECIFICATION

- Rated Voltage: 6 V
- Operating Voltage Range 2~7.5V
- Gear reduction ratio: 99:1
- Gearbox length: 23 mm
- "D" shape shaft diameter: 4 mm
- No-load speed: 15 RPM @ 6V
- No-load current: 50 mA
- Locked-rotor torque: 2.5 Kg.cm
- Locked-rotor current: 0.6 A
- Operating Temperature: -20～60℃
- Weight: 72 g


SHIPPING LIST

- Metal DC Geared Motor - 6V 15RPM 10Kg.cm x1

Downloaded from Arrow.com.

REVIEW

FAQ



Sign up for exclusive offers!

Your email address →

Like us on

DFROBOT® DRIVE THE FUTURE

INFORMATION

- About Us
- Warranty
- Privacy Policy
- Shipping
- Payment
- FAQ

CUSTOMER SERVICE

- DFRobot Distributors
- Contact us
- Site Map

MY ACCOUNT

- Affiliates
- Specials
- Coupon

Downloaded from Arrow.com.