



2-1969540-6 Product Details

Share

Print

Email



Active

View 3D PDF

Economy Power Connectors

HOUSING, PLUG, DUAL ROW, EP2.5

2-1969540-6

TE Internal Number: 2-1969540-6

Product Highlights

View All

- Economy Power 2.5 Product Line
- Connector
- Wire-to-Wire
- Applies To Wire/Cable
- 26 Positions

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Line	Economy Power 2.5
Product Type	Connector
Connector Type	Housing
Sealed	No

Mechanical Attachment

Mating Retention Type	Latch(ing)
-----------------------	------------

Electrical Characteristics

Operating Voltage Reference	AC
Operating Voltage (VAC)	250

Dimensions

Profile Height (Y-Axis) (mm [in])	8.30 [0.326]
-----------------------------------	--------------

Body Features

Mating Retention	With
------------------	------

Contact Features

Contact Type	Socket
--------------	--------

Housing Features

Centerline (mm [in])	2.50 [0.098]
Connector Style	Plug
Housing Color	White
Housing Material	Nylon - GF

Configuration Features

Number of Positions	26
Number of Rows	2

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Environmental

Operating Temperature (°C [°F])	-55 – +105 [-67 – +221]
---------------------------------	-------------------------

Conditions for Usage

Applies To	Wire/Cable
Glow Wire Rating	Standard Part - Not Glow Wire

Operation/Application

Application Use	Wire-to-Wire
-----------------	--------------

Packaging Features

Packaging Method	Bag/Box
------------------	---------

Other

Brand	TE Connectivity
-------	-----------------

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

