

## M12 transf. recpt. rear mounting kit



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 301 2007
Specification	M12 transf. recpt. rear mounting kit
HARTING eCatalogue	<a href="https://harting.com/21033012007">https://harting.com/21033012007</a>

### Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	Housing
Description of the accessory	for rear mounting

### Version

Gender	Female
Locking type	Screw locking

### Technical characteristics

Tightening torque	2 Nm Lock nut
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition

### Material properties

Material (accessories)	Brass, nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead



**Pushing Performance**  
Since 1945

## Material properties

ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

## Commercial data

Packaging size	30
Net weight	26.561 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140236424
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400