



**Part Number :** [747641201](#)  
**Product Description :** QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 2.0m Length  
**Series Number :** 74764  
**Status :** Active  
**Product Category :** High-Speed I/O Cable Assemblies




## Documents & Resources

**Drawings**  
[747641201\\_sd.pdf](#)  
[PK-74764-1201-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains TBBA per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	74764
Description	QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 2.0m Length
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	QSFP+-to-4 SFP+
Product Name	QSFP Plus,QSFP+,SFP Plus,SFP+
Type	Pluggable
UPC	884982451551

### Electrical

Data Rate	10.0 Gbps
Impedance	100Ω

### Physical

Cable Bundling	None
Cable Length	2.0m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Net Weight	368.000/g
Packaging Type	Bag
Release Style	Pull Tab
Single Ended	No
Wire/Cable Type	Twinax
Wire Size (AWG)	30

---

---

This document was generated on Mar 03, 2025