



Part Number : [367693070](#)
Product Description : Pre-Crimped Lead Micro-Fit+ Male-to-Pigtail, 1.50µm Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black
Series Number : 36769
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings
[367693070 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	36769
Description	Pre-Crimped Lead Micro-Fit+ Male-to-Pigtail, 1.50µm Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Fit+ Terminal-to-Pigtail
Keyword	Pre-Crimped Leads
Product Name	Micro-Fit+
UPC	196823603631

Electrical

Current - Maximum per Contact	7.8A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Male-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.879/g
Packaging Type	Bag

Plating min - Mating	1.500µm
Plating min - Termination	1.500µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	24

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit+ Dual Row Plug Housings	<u>215922</u>

This document was generated on Apr 13, 2026