



1. Wiring Diagram.



2. Cable test condition :

Open / Short : 100%

Insulation resistance : 5M ohms

Contact resistance : 2 ohm

Hipot : DC 300V / 1 sec

3. Each pcs with PE polybag.

7	COPER	W25MM*1.45MM	1	
6	COPER	W20MM*1.35MM	1	
5	PVC	45P PVC BLACK OVERMOLD	25g	
4	PE	LLDPE 500026 6201 INSIDE MOLDING	16g	
3	CONN	HDMI C TYPE MALE PIN G/F, SHELL PLATED NICKEL, INSULATION BLACK	1	P2
2	CONN	HDMI A TYPE MALE PIN G/F, SHELL PLATED NICKEL, INSULATION BLACK	1	P1
1	CABLE	UL20276 《30AWG (7/0.1TS) *I+EA+AL/MY》 *4+30AWG (7/0.1TS) *5C +AEM(16/6/0.12AM) OD6.0 BLACK	1	5000mm
NO.	PART NO.	DESCRIPTION	QTY	UNIT/REF

BILL OF MATERIAL

A	INITIAL RELEASE	2017/7/26
REVECHN#	DESCRIPTION	DATE
Cnc Tech,LLC	HDMI A/M TO HDMI C/M CABLE	742-10010-00500
DRAWN EDWIN LAI	DATE 07/26/17	CUSTOMER P/N:
CHECKED W/in.C	DATE 07/26/17	CUSTOMER:
APPROVAL		SHEET 1 OF 1

