

M17 Crimp Contact 1,5mm,FE ,0,25-0,5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 074 0000
Specification	M17 Crimp Contact 1,5mm,FE ,0,25-0,5mm ²
HARTING eCatalogue	https://harting.com/21170740000

Identification

Category	Contacts
Series	Circular connectors M17
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.25 ... 0.5 mm ²
Conductor cross-section [AWG]	AWG 24 ... AWG 20
Stripping length	7 mm
Limiting temperature	-40 ... +125 °C

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

Commercial data

Packaging size	100
Net weight	0.5 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140819702
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522