

[Honeywell.com](#) [Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)

Honeywell Sensing and Control

[Search](#)**2450RG 82040035**

(Home : Products : Sensors » Thermostats » 2450RG)

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9781)
- Wireless (45)

Technology

- Electromechanical (9307)
- Magnetic (541)
- Microstructure (1495)
- Optical/Infrared (1042)
- Thick Film (1409)
- More...

new products**New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)**white papers**

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters



2450RG Series Phenolic Automatic Reset Thermostats

*Actual product appearance
may vary.*

[Sales & Service](#)[Distributor Inventory](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)**Product Specifications**

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	0.5 A
Voltage	250 Vac/50 Vdc
Operating Temperature	0 °C to 150 °C [32 °F to 302 °F]
Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]
Open Temperature	99.4 °C [211 °F]
Close Temperature	80.0 °C [176 °F]
Open Tolerance	3.9 °C [7 °F]
Close Tolerance	4.4 °C [8 °F]
Dielectric Strength	MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Housing Material	Phenolic
Contact Material	WE -1 gold alloy cross point
Agency Approvals and Standards	UL, CSA
Mounting	B213 fixed bracket
Series Name	2450RG

contacts

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

[meet dr. larry](#)

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

[Meet Dr. Larry](#)**my links**

[Login to iCOM](#)
[Login to Rep/AD Portal](#)
[Login to Digital University](#)

News Center

HONEYWELL INTRODUCES MICROPower OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT
HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

MICRO SWITCH Anniversary site**Need help?**[Click here to contact us](#)[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)