




PART NUMBER
10159556-L2000LF

OCTIS USB2.0 TYPE A PLUG CABLE ASSEMBLY






SL NO	ITEM DESCRIPTION
1	PLUG CAP
2	PLUG KIT ASSEMBLY
3	CABLE



spec ref				dr		Varghese, Bone		2020/10/21		projection		MM		size		A3		scale		3:10	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Ajith James		2020/10/21						ecn no -					
ISO 406																					
ISO 1101						chr		-		-											
surface -  ISO 1302		linear		0.X		±0.3		Amphenol FCi		title		OCTIS USB 2.0 TYPE A PLUG KIT		dwg no		10159556		rev		A	
				0.XX		±0.13															
				0.XXX		±0.05															
		angular		0°		±°															

BOARD CONNECTOR WITH BULK HEAD DETAILS





- NOTES:
1. RECOMMENDED BOARD CONNECTOR: REFER DRAWING 10158276
 2. REFER DRAWING 10157693 FOR BULK HEAD DETAILS
 3. UNLESS OTHERWISE SPECIFIED, LABEL CONTENT SHALL CONTAINS:
 - AMPHENOL FCI PART NUMBER
 - LOT CODE
 - COUNTRY OF ORIGIN

PLUG DETAILS

1. HOUSING; PBT30%GF, COLOUR: WHITE
2. TERMINAL: BRASS
3. PLATING: 30μ" Au
4. WITHSTAND VOLTAGE: 500V AC
5. RATED CURRENT: 1.5A

CABLE DETAILS

1. 1P*28AWG + 2C*20AWG + AL.MYLAR+DRAIN+BRAID
2. TINNED COPPER
3. INSULATION: HD-PE AND SR-PVC
4. OUTER JACKET: HALF MATT PVC COLOUR: BLACK, OD: 4.8±0.2MM

spec ref				dr	Varghese, Bone	2020/10/21	projection 	MM 	size	A3	scale	3:10	
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Ajith James	2020/10/21			ecn no				-
				chr	-	-			rel level				Released
				appr	Kuriakose, San	2020/10/21	product family		OCTIS				
surface  ISO 1302	linear	0.X	±0.3	Amphenol FCi	title	OCTIS USB 2.0 TYPE A PLUG KIT			dwg no	10159556		rev	A
		0.XX	±0.13										
		0.XXX	±0.05			OCTIS 26MM PITCH							
	angular	0°	±°										
				cat. no.	-	Product - Customer Drw				sheet 2 of 2			