

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210400297](#)
Status: **Active**
Overview: [mPm DIN Valve Connectors](#)
Description: mPm DIN Valve Connector, Form B - 11mm, 2 Pole Plus Ground Position H6, to 1.0m (3.28') PVC Cable Pigtail, Black Nitrile Gasket, 250V

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E218123
General	
Product Family	Industrial Cordsets
Series	121040
Connector End A	Brad mPm DIN B - 11mm
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Protocol	N/A
Region	America, Europe
Type	Single Ended
UPC	883906581015
Physical	
Cable Diameter	5.72mm (.225")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	5.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	E162N3N10061
Reference - Drawing Numbers	
Sales Drawing	1210400254-000, SD-121040-008



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[121040](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION