

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0987891101

Status:

Active - Custom

Description:

NSCC single part, Non Sealed, 1.5mm, Male Housing, 10 Circuits, Dual Row, Black

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Crimp Housings

Series

98789

Application

Power

Product Name

NSCC

Physical

Circuits (maximum)

10

Color - Resin

Black

Gender

Male

Glow-Wire Compliant

No

Lock to Mating Part

Yes

Number of Rows

2

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

4.25mm (.167")

Pitch - Termination Interface

6.00mm (.236")

Polarized to Mating Part

Yes

Ports

1

Stackable

No

Temperature Range - Operating

-40°C to +120°C

Material Info

Old Part Number

07411EV10F1

Reference - Drawing Numbers

Sales Drawing

SD-98789-002



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

98789Series

Mates With

987881081 , Link987881088

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION