

product details

Product Searches

- [7/16](#)
- [1.0/2.3](#)
- [1.6/5.6](#)
- [AFI](#)
- [AMC](#)
- [BNC / RP-BNC](#)
- [C](#)
- [FAKRA SMB](#)
- [FME](#)
- [HN](#)
- [MCX](#)
- [Mini-UHF](#)
- [Mini 75 ? SMB](#)
- [MMCX](#)
- [Precision \(APC\)](#)
- [QMA](#)
- [SC](#)
- [SlimLine BNC](#)
- [SMA / RP-SMA](#)
- [SMB](#)
- [SMC](#)
- [SMP](#)
- [SSMB](#)
- [TNC / RP-TNC](#)
- [Triax](#)
- [True 75 ? BNC](#)
- [Tw in BNC](#)
- [Tw inax](#)
- [Type F](#)
- [Type G](#)
- [Type N](#)
- [UHF](#)
- [Reverse Polarity](#)



Please note: Images are for reference only

Amphenol Part Number:	031-15
Product Series:	BNC
Product Type:	Connectors » Cable
Application:	Clamp
Body Plating:	Nickel
Body Termination:	Clamp
Cable Group:	E
Cable Type:	Belden 8241 , Belden 8279 , RG-140 , RG-59
Connector Body Style:	Straight
Contact Plating:	Silver
Contact Termination:	Solder
Gender:	Jack
Grade:	Industrial
Impedance:	50 Ohm
RoHS Certificate:	Yes
More Information:	Assembly Instructions
	Customer Drawing
	Distributor Inventory

- [Adapters](#)
- [Cable Assemblies](#)
- [Tools](#)
- [Accessories](#)

[Product Search](#)

[Inventory Search](#)