



YGHS28 Compression Grounding Splice, 4/0 AWG Cu

By Burndy
Catalog # [YGHS28](#)

HYGROUND® Grounding Irreversible Compression Splice



Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	• UL467 • UL 486A-486B • IEEE 837
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	66 mm
Dimension - Outside Diameter inch	0.89 in
Dimension - B Length fraction	1-1/6 in
Dimension - B Length inch	1.18 in
Dimension - Length Overall inch	2.59 in

General

Trade Name	HYLINK™
Die Index	17
Plated	N
Sub Brand	HYLINK
UPC	781810220474
Type	Splices
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220474
UPC 14 Digit GTIN	00781810220474

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5760
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)