

CT3158

BNC male to Alligator Clip

BNC male coaxial connector to alligator clip breakout cable Molded...

Description

BNC male coaxial connector to alligator clip breakout cable.
Standard BNC connector with molded bend relief boot. Cable is
high quality 50 RG-58C/U.

Breakout leads 20 AWG wire with black and red insulated
alligator clips, 4.5" (12 cm) in length

- BNC center conductor, gold plated



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

Voltage Max.	500 Vrms
Current Max.	3 A
Impedance	50
Cable Type	RG-58C/U
Temperature (degrees)	0 to +50C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

