

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1212020001

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket



Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-121201-001-001 \(PDF\)](#)

[Product Specification STR-1251-001 \(PDF\)](#)

[Packaging Specification PK-121202-C22-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

|                               |                                 |
|-------------------------------|---------------------------------|
| General                       |                                 |
| Product Family                | Field Attachable / Accessories  |
| Series                        | 121202                          |
| Form                          | B - 11mm                        |
| IP Rating                     | IP65, IP67                      |
| Material - Contact            | Brass                           |
| Overview                      | mPm DIN Valve Connectors        |
| Product Name                  | mPm                             |
| Type                          | Field Attachable Connector      |
| UPC                           | 884982012448                    |
| Physical                      |                                 |
| Cable Diameter                | N/A                             |
| Coupling Type                 | External Thread                 |
| Diagnostics / LEDs            | No                              |
| Diagnostics Port              | No                              |
| Gender                        | N/A                             |
| Keyway                        | None                            |
| Material - Connector Body     | Polyamide                       |
| Material - Coupling Nut       | N/A                             |
| Material - Plating Mating     | Silver                          |
| Net Weight                    | 19.522/g                        |
| Orientation                   | 90° Angle                       |
| Pitch - Mating Interface      | 11.00mm                         |
| Poles                         | 2                               |
| Temperature Range - Operating | -40°C to +90°C                  |
| Wire Size AWG                 | N/A                             |
| Electrical                    |                                 |
| Current - Maximum per Contact | 16.0A                           |
| Voltage - Maximum             | 250V AC / 300V DC               |
| Material Info                 |                                 |
| Engineering Number            | C22200N0R                       |
| Reference - Drawing Numbers   |                                 |
| Packaging Specification       | PK-121202-C22-001               |
| Product Specification         | PS-121201-001-001, STR-1251-001 |
| Sales Drawing                 | SD-121202-001                   |

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121202 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION