


HBL2423 -- Twist-Lock Connector Body



3P4W, 20A 3PH 250V, L15-20R, Black & White Nylon

Product Specifications

| | |
|--------------------------------------|---|
| Product Type | <p>Twist-Lock Devices</p> |
| Product Item | Connector Body |
| Wiring Scheme | 3-Pole, 4-Wire Grounding |
| Amperage | 20A |
| Voltage | 3 Phase 250V AC |
| NEMA Configuration | L15-20R |
| Item Style | Insulgrip |
| Device Color | Black/White |
| Cord Dia. | .35"-1.15" (9-29) |
| Terminal Retainer Material | Clear polycarbonate |
| Housing Material | Black nylon |
| Cord Clamp Material | Natural (white) nylon |
| Terminal Clamp Material | .08" (2) steel-nickel plated |
| Terminal Screw Material | #10-32 Brass (white finish on neutral screw when used) Multi-drive |
| Ground Screw Material | #10-32 Brass (green finish) Multi-drive |
| Cord Clamp Screw Material | Steel, zinc plated Multi-drive |
| Body Holding Screw Material | Steel, zinc plated Multi-drive |
| Body Contact Carrier Material | Natural White Nylon |
| Contact Spring Material | Brass |
| Spring Binding Plate Material | Brass |
| Ground Contact Material | .031" (.8) Brass |
| Ratings | Molded In or Stamped On |
| Catalog No | Permanently ink marked on product |
| Dielectric Voltage Withstand | 2,000V minimum |
| Current Interrupting | Certified for current interrupting a full rated current |
| Temperature Rise | Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75. |
| Cord Accommodation | Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49. |
| Terminal Accommodation | 20A #12 AWG |
| Terminal Identification | Terminals identified in accordance with UL 498 (X, Y, Z, White, Green) |
| Flammability | HB or better per UL 94 or CSA 22.2 No. 0.6 |
| Operating Temperatures | Maximum Continuous 75 C Minimum -40 C (w/o impact) |
| Moisture Resistance | IP20 |
| Listings | FED SPEC UL/CSA |
| UPC Number | 783585038216 |
| Weight in LBs | 0.4 |
| Link to Drawing Library | Click here for Library |
| Link to PDF Catalog | Click here for Catalog |



NEMA L15-20P
20A 3Ø 250V AC
UL/CSA
3 HP

NEMA Configuration

