



- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

how to purchase

-  [sales contacts](#)
-  [stock check](#)

 [search](#)

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators 

[find](#) 

Part # / Text Search

Part No.:

Text Search:

[search](#) 

quick links

Dialight Corporate Video


Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators		
P/N# 5600206F	Bi-Pin LED Lamp Single Color	
Description	Bi Pin LED Lamp	
Package Options	25 Pieces Per Bag	
Product Type	Through Hole Indicators	
Sub Product Type	Discrete LED	
Configuration	Bi-Pin LED Lamp	
Lamp Type	Single Color	
Viewing	Top View	
Viewing Angle	50	

Absolute Maximum Ratings (Ta = 25 °)	
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



Operating Characteristics		
LED Position		
Color	Green	
Lamp Type	Single Color	
LED Type	Resistor	
Intensity Min (mcd)		
Intensity Typ (mcd)	5.8	
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)	570	
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)		
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		

Distributor Stock Check

Check stock with our distributors now.

5600206F

[check stock](#) 