



# CH8M, Cable Tie Hanger, 1000 pieces, Natural

By Burndy  
Catalog # CH8M

Nylon Cable Hanger



## Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| Certification - UV Rated      | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Configuration

|                 |       |
|-----------------|-------|
| Mounting Method | Screw |
|-----------------|-------|

## Dimensions

|                |           |
|----------------|-----------|
| Package Height | 0.000 in  |
| Package Weight | 0.000 lb. |

|                             |          |
|-----------------------------|----------|
| Dimension - Width mm        | 12 mm    |
| Dimension - Width inch      | 0.48     |
| Package Length              | 0.000 in |
| Package Width               | 0.000 in |
| Dimension - Bundle Diameter | .54      |
| Max inch                    |          |

## General

|                   |                |
|-------------------|----------------|
| Color             | Natural        |
| Trade Name        | UNIRAP™        |
| UPC               | 781810336335   |
| Material          | Nylon 6/6      |
| UPC 14 Digit GTIN | 00781810336335 |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 5000  |
| Pallet Quantity       | 99999 |
| Carton Quantity       | 1000  |
| Packaging Type        | Bag   |

## Product Assets

[Catalog \[English\]](#)