

Representative Image

Catalog No. B14-250

Description: NON-INS FEM .250x.032 DISC 16-14AWG

UPC No 786210803340

Home > Connectivity & Grounding > Sta-Kon > Wire terminal disconnect

Non-Insulated Female Disconnect, Length .73 Inches, Width .31 Inches, Tab Size .250x.032, Wire Range #16-#14 AWG, Copper, Tin Plated

Descriptors

Category	Wire terminal disconnect
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

Specifications

Material	Brass
Finish	Tin Plated
Color	Metallic
Insulation	None

Classifications

Brand Name	Sta-Kon
Standard	UL E66716

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Not isolated
Material	Copper
AWG-range	16-14

by ABB

Downloaded from Arrow.com.

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622701	N/A	N/A	N/A
CSA	7222	622701	N/A	N/A	N/A
UL	E66716	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.