

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301180028](#)
Status: **Active**
Overview: [Aero-Motive Box-Track Festoon Systems](#)
Description: Box Track, Festoon Tow Car - 5414

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Festoons
Series	130118
Cable Height - Maximum	19.05mm (.750")
Cable Width - Maximum	98.00mm (3.858")
Combined Cable Weight-Max./Car	24.95kg (55.0 lb)
Component Type	Car - Lead
Depth	89.92mm (3.540")
Duty	Standard - 25kg per Car
Exclude SD Check	Yes
Height	144.78mm (5.700")
Length	250.0m (820.0')
Overview	Aero-Motive Box-Track Festoon Systems
Product Name	Aero-Motive
Type	Box Track
UPC	78678863201
Physical	
Material - Coating	Zinc
Material - Metal	Galvanized Steel
Net Weight	226.790/g
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	156.46mm (6.160")
Thread Size	N/A
Wire/Cable Type	Flat
Material Info	
Engineering Number	54143

Image coming soon

Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130118](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION