


① only for four indent crimping tool adjusting Ø0,1



part no.		ØD	wire gauge		stripping length	
silver plated	gold plated		mm²	AWG		
09 15 000 6204	09 15 000 6224	0,90	0,14-0,37	26-22	8	
09 15 000 6203	09 15 000 6223	1,10	0,5	20		
09 15 000 6205	09 15 000 6225	1,30	0,75	18		
09 15 000 6202	09 15 000 6222	1,45	1	18		
09 15 000 6201	09 15 000 6221	1,75	1,5	16		
09 15 000 6206	09 15 000 6226	2,25	2,5	14	6	
09 15 000 6207	09 15 000 6227	0,90	0,14-0,37	26-22	8	

	All Dimensions in mm Original Size DIN A4		Scale 2:1	Free size tol.		Ref. Sub. TB 09 15 000 62.. v. 16.06.10	
	All rights reserved Department EL PD - DE		Created by RULLKOETTER	Inspected by SCHNIEDER	Standardisation TIEMANNA	Date 2014-05-20	State Final Release
HARTING Electric GmbH & Co. KG D-32339 Espelkamp		Title Han D crimp contacts female					Doc-Key / ECM-Nr. 100109246/UGD/004/A 500000075030
		Type TB	Number 09 15 000 62XX				Rev. A Page 1/1