
Data sheet

H4,0/18 GR SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- In multi-pack bag
- Weidmüller colour code
- Other colour code

General ordering data

Version	Wire-end ferrule, Standard, 12 mm, 10 mm, grey
Order No.	9026010000
Type	H4,0/18 GR SV
GTIN (EAN)	4008190117382
Qty.	250 items
Packaging	Multipack bag

Downloaded from Arrow.com.

Data sheet

H4,0/18 GR SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.29 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule with plastic collar, grey	Version	Standard

Wire-end ferrules

Contact surface diameter (D1)	2.8 mm	Contact surface length (L2)	10 mm
Collar diameter (D2)	4.8 mm	Plastic collar thickness (S2)	0.3 mm
L1 in mm	18.00 mm	Wire connection cross section AWG, max.	AWG 12
Metal sleeve thickness (S1)	0.2 mm	Stripping length	12 mm
Conductor cross-section	4 mm²	Colour code	Weidmueller

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		


Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing



Downloaded from Arrow.com.