



Part Number : [191890015](#)

Series Number : 19189

Product Category : Splices

Product Description : Krimptite Butt Splice for 10-12 AWG Wire

Status : Active

Engineering Number : C-146

---

## Documents & Resources

### Drawings

[Drawing 191890015\\_sd.pdf](#)

### Specifications


[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2024)4144-DC (27 June 2024)                                       |
| EU RoHS            | Compliant per EU 2015/863   |

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### [EU RoHS Certificate of Compliance](#)

---

## Part Details

### General

|                |  |
|----------------|--|
| Status         | Active                                   |
| Category       | Splices                                  |
| Series         | 19189                                    |
| Description    | Krimptite Butt Splice for 10-12 AWG Wire |
| Product Family | Splices                                  |
| Product Name   | Butt,Krimptite                           |
| UPC            | 800755048872                             |

### Agency

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E32244  |

### Physical

|                                |         |
|--------------------------------|---------|
| Barrel Type                    | Closed  |
| Insulation                     | None    |
| Material - Metal               | Copper  |
| Material - Plating Mating      | Tin     |
| Material - Plating Termination | Tin     |
| Net Weight                     | 1.742/g |
| Packaging Type                 | Bag     |
| Wire Size (AWG)                | 10, 12  |

---

## Application Tooling

### Global

| Description  | Part Number      |
|--|------------------|
| PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup> | <u>640030100</u> |
| Crimp Head for the AT-200 Pneumatic Hand Tool  | <u>640070100</u> |
| ServiceGrade Hand Crimp Tool - Ratchet   | <u>640160038</u> |

---

This document was generated on Jul 29, 2024