

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Cable Assembly
- ? Fiber Type = SM
- ? Cable Assembly Type = SC -UPC to SC-UPC
- ? SC Connector
- ? Singlemode

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

[CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE 2.9mm OFNR C...](#)
(PDF, English)

? None Available

? None Available

? None Available

? None Available

? None Available

? Product Line Information

? Tooling

List all Documents

- ? Product Type = Cable Assembly
- ? Cable Assembly Type = SC -UPC to SC -UPC
- ? Connector = SC
- ? Comment = Insertion Loss: 0.50 dB Max., 0.2 dB Max. Typical, when measured against a Reference Lead.; Ultra Polished Connector (UPC)

- ? Mode = Singlemode
- ? Insertion Loss (dB) = 0.40

- ? Fiber Type = SM
- ? Cable Diameter (mm [in]) = 3.00 [.118]
- ? Number of Fibers = 1
- ? Flammability Rating = Riser (UL OFNR/CSA FT 4)
- ? Cable Color = Yellow
- ? Length (M [ft]) = 0.46 [1.509]
- ? Ferrule Material = Ceramic
- ? Return Loss (dB) = 55

```
? Boot Body Style    - Left = Long
? Boot Color        - Left = Blue
? Boot Body Style    - Right = Long
? Boot Color         - Right = Blue
? Fibre Channel = No
```

- ? Cable Type = Simplex
- ? Cable Buffering = Tight
- ? Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Brand = Tyco Electronics