

preLink M12 housing empty



Image is for illustration purposes only. Please refer to product description.

Part number	20 82 000 1210
Specification	preLink M12 housing empty
HARTING eCatalogue	https://harting.com/20820001210

Identification

Category	Connectors
Series	preLink® Circular connectors M12
Element	Empty housing
Type of hood/housing	Screw mounted housing

Version

Gender	Male
Locking type	Screw locking

Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	5 ... 9.5 mm
Vibration resistance	5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

Page 1 / 2 | Creation date 2026-05-15 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	EN 45545-2
UL / CSA	UL 1863 DUXR2.E470046 CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	62 g
Country of origin	Latvia
European customs tariff number	85389099
GTIN	5713140135499
eCl@ss	27440224 Shell for circular connectors
ETIM	EC003556
UNSPSC 24.0	39121405