



M-Class Mark II Features

M-Class Series Mark II

- Compact, industrial-strength table-top bar code or RFID printer
- Designed for those who need the power of an industrial printer but have limited space – M-Class printers are 30% smaller than the competition
- Best warranty in the industry
- Quick media loading and easy serviceability reduces total cost of ownership

	M-4206 Mark II	M-4206 (OLD)	M-4210 Mark II	M-4208 (OLD)
				
List Price	starting at \$1145	starting at \$1195	starting at \$1495	starting at \$1495
Standard Memory	8MB RAM / 4MB Flash	4MB RAM / 2MB Flash	16MB RAM / 8MB Flash	8MB RAM / 2MB Flash
Memory Options	4MB Flash	4MB Flash	64MB Flash	6 MB Flash
Media Width	0.75" - 4.65" (19mm – 118mm)	0.75" - 4.65" (19mm – 118mm)	0.75" - 4.65" (19mm – 118mm)	0.75" - 4.65" (19mm – 118mm)
Speed	6ips	6ips	10ips	8ips
Resolution	203dpi	203dpi	203dpi	203dpi
Standard Connectivity	Serial RS232, Parallel, USB	Serial RS232, Parallel, USB	Serial RS232, Parallel, USB	Serial RS232, Parallel, USB
RFID Option	n/a	n/a	UHF or HF	n/a
Standard Graphics Display	128x64 graphical display 3 button/3 LED	3 button/3 LED	128x64 graphical display 3 button/3 LED	2 line LCD Display 3 button/3 LED
Printhead	IntelliSEAQ™	Standard	IntelliSEAQ™	Standard
Emulation	PL-Z	n/a	PL-Z	n/a
MCL	Optional w/ added Flash	n/a	Optional	n/a
Options	Present sensor, Peel & Present, Cutter, Internal Rewind, LAN, Wireless	Cutter, Rewind, Ethernet	Present sensor, Peel & Present, Cutter, Internal Rewind, LAN, Wireless, USB Host	Cutter, Rewind, Ethernet
Warranty	Printer: 2 years, 2 million linear inches Printhead: 1 year, 1 millions linear inches	Printer: 2 years, 2 million linear inches Printhead: 1 year, 1 millions linear inches	Printer: 2 years, 2 million linear inches Printhead: 1 year, 1 millions linear inches	Printer: 2 years, 2 million linear inches Printhead: 1 year, 1 millions linear inches
Compare With	Zebra S4M, Intermec PD41	Zebra S4M, Intermec PD41	Zebra Z4M	Zebra Z4M

Contact your Datamax representative with any questions regarding this information. Datamax Corporation assumes no responsibility for errors or omissions in this Bulletin. This Bulletin is not a contract or offer to sell. All prices and products stated herein are subject to change without notice.
4501 Parkway Commerce Blvd. • Orlando • Florida • USA • (407) 578-8007 • www.datamaxcorp.com



Cross Reference List – New vs Old Part Numbers

New CID	Old CID	New Description
KB2-00-48000000	K12-00-18000000	M-CLASS, M4206, 4", 203 DPI, DT/TT, 6 IPS, metal cover, graphics display
KB2-00-48040000	K12-00-18040000	M-CLASS, M4206, 4", 203 DPI, DT/TT, w/cutter, metal cover, graphics display
KB2-00-48000000	K12-00-38000000	M-CLASS, M4206, 4", 203 DPI, DT/TT, metal cover, graphics display
KB2-00-08000000	K12-00-08000000	M-CLASS, M4206, 4", 203 DPI, DT, 6 IPS, metal cover, graphics display
KB2-00-08040000	K12-00-08040000	M-CLASS, M4206, 4", DT, w/cutter, metal cover, 203 DPI, 4MB FLASH
KB2-00-48400000	K12-00-18400000	M-CLASS, M4206, 4", 203 DPI, 6 IPS, internal rewind, DT/TT, metal cover, graphics display
KB2-00-48900000	K12-00-18900000	M-CLASS, M4206, 4", 203 DPI, 6 IPS, DT/TT, castpeel&prst, internal rewind, metal cover, graphics display
KB2-00-08900000	K12-00-08900000	M CLASS, M4206, 4", DT, peel&prst, internal rewind, metal cover, graphics display
KB2-00-08000L00	Not offered	M CLASS, M4206, 4", 203 DPI, 6 IPS, DT, Ethernet, metal cover, graphics display
KB2-00-48000L00	Not offered	M CLASS, M4206, 4", 203 DPI, 6 IPS, DT/TT, Ethernet, metal cover, graphics display
KJ2-00-48000007	K22-00-38000001	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, 8MB FLASH, metal cover, graphics display
KJ2-00-48040L07	K22-00-18040L01	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, cutter, Ethernet, metal case, graphics display
KJ2-00-08000L07	K22-00-08000L01	M-CLASS, M4210, 4", 203 DPI, 10 IPS, DT, 8MB, Ethernet, metal cover, graphics display
KJ2-00-08000007	K22-00-08000001	M-CLASS, M4210, 4", 203 DPI, 10 IPS, DT, 8MB, metal cover, graphics display
KL2-00-48000L07	K52-00-38900L01	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, 64MB FLASH, Ethernet, metal cover, graphics display
KJ2-00-08400L07	K22-00-08400L01	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT, 8MB FLASH, internal rewind, Ethernet, metal cover, graphics display
KJ2-00-08000L07	K22-00-08000L00	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT, 8MB FLASH, Ethernet, metal cover, graphics display
KL2-00-48000L07	K52-00-18000L01	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, 64MB FLASH, Ethernet, metal cover, graphics display
KJ2-00-48000007	K22-00-18000000	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, 8MB FLASH, metal cover, graphics display
KJ2-00-48400007	K22-00-18400001	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, 8MB FLASH, internal rewind, metal cover, graphics display
KJ2-00-48900007	K22-00-18900001	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, castpeel&prst/INT RW, METAL COVER, graphics display
KJ2-00-48900L07	K22-00-18900L01	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, castpeel&prst/internal rewind, Ethernet, metal cover, graphics display
KJ2-00-48000L07	K22-00-18000L01	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, 8MB FLASH, Ethernet, metal cover, graphics display
KJ2-00-48000L07	K22-00-18000L00	M CLASS, M4210, 4", 203 DPI, 10 IPS, DT/TT, 8MB FLASH, Ethernet, metal cover, graphics display

Contact your Datamax representative with any questions regarding this information. Datamax Corporation assumes no responsibility for errors or omissions in this Bulletin. This Bulletin is not a contract or offer to sell. All prices and products stated herein are subject to change without notice.
4501 Parkway Commerce Blvd. • Orlando • Florida • USA • (407) 578-8007 • www.datamaxcorp.com