


S-8 Single Contact Bayonet Base



*Long Life
**Silver Bonnet
***Black Bonnet

Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
1459	4.00	.80	2.5	300	C-2R
1651	5.00	.60	3.0	20	C-2R
1611	5.40	1.86	10.0	1,000	C-6
1613	6.00	1.50	13.0	50	C-6
1680	6.00	4.10	32.0	300	C-6
1129	6.40	2.63	21.0	200	C-6
1605	6.40	2.69	21.0	200	C-2V
87L	6.65	2.04	15.0	500	C-2R *
1619	6.70	1.90	15.0	500	C-6
87	6.80	1.91	15.0	300	C-2R
1295	12.50	3.00	50.0	200	C-2R
93	12.80	1.04	15.0	500	C-2R
199	12.80	2.25	32.0	1,200	C-6
1073	12.80	1.80	32.0	200	C-6
1093	12.80	1.19	15.0	1,000	C-2R
1141	12.80	1.44	21.0	500	C-6
1156	12.80	2.10	32.0	600	C-6
1159	12.80	1.60	21.0	500	C-6
1161	12.80	1.35	22.0	500	CC-6
1777	12.80	1.52	26.0	400	C-2R
2396	12.80	2.23	40.0	400	C-6
91	13.00	.71	10.0	500	C-2R
1095	14.00	.51	4.0	5,000	C-6
305	28.00	.51	15.0	300	C-2V
307	28.00	.67	21.0	300	C-2V
315	28.00	.90	32.0	300	C-2V
705	28.00	.51	15.0	900	CC-6
1203	28.00	.71	21.0	400	C-2V
1563	28.00	.76	21.0	1,000	CC-6
1580	28.00	.93	32.0	400	CC-6
1591	28.00	.61	15.0	1,000	C-2V
1665	28.00	.80	21.0	1,000	C-2V
1683	28.00	1.02	32.0	500	2C-6
1691	28.00	.61	15.0	1,000	2C-2R
2232	28.00	.64	18.0	2,000	CC-81
2232SB	28.00	.64	-	2,000	CC-81**
2233	28.00	.77	21.0	2,000	CC-81
F674	28.00	.77	-	2,000	CC-81***
W674	28.00	.77	-	2,000	CC-81**
109	44.00	.17	6.0	200	C-7A