

Precautions for use

General notes

ML-850-VBY

made in JAPAN



Pitch 8mm

for power supply

Solid wire only

2012-12-26

Notice of partial product changes. PDF



See other change notifications



E101073



R50047802



Order model number

Order model number

ML-850-VBY

Basic information

Dimension

Soldering heat resistance conditions

Download

Basic information

Rating	250V-20A
Insulation resistance	DC500V、1000MΩ Min
Withstand voltage	AC2000V (1minute)
Certificates & Approvals	UL (Approved for field wiring)・CSA (C-UL)・TÜV (Compliant with IEC60947-7-1)
Position	2
Main insulator	PBT (UL94V-0)
Button insulator	PBT (UL94V-0)
Rating wire	Solid wire : Φ2.0mm (AWG12)
Wire range	Solid wire : Φ1.6mm～Φ2.0mm (AWG16～AWG12)
Terminal type	PC terminal
Wire strip length	14mm
Body color	GY (Gray)
Button color	B (Black)
Applicable tool for button	Screw driver or others
PCB thickness	1.6mm
Note	1.Fluororesin is applied to the buttons to facilitate the operation of the buttons. It may appear that white foreign matter has adhered due to the concentration and retention of this fluororesin in the concave parts of the button operation part, but there is no problem with the quality.
Caution	1.Don't immerse and wash this product in liquid.

List of partial product change notifications

2012-12-26	Notice of partial product changes. PDF
2012-09-13	Notice of partial product changes. PDF

Home

Product search

Product Category

About SATO PARTS

News classification

Contact us

Video channel

Download brochure

Environmental initiatives

Privacy policy

Download terms

Terms of Use