



Pushing Performance
Since 1945

Har-speed M12 malecont. Crimp AWG 24-28



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9014
Specification	Har-speed M12 malecont. Crimp AWG 24-28
HARTING eCatalogue	https://harting.com/21011009014

Identification

Category	Contacts
Series	har-speed
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section (mm²)	0.08 ... 0.22 mm²
Conductor cross-section (AWG)	AWG 28 ... AWG 24
Performance level	1

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	100
Net weight	0.095 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140136700
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522