



HEAT-SHRINK BOOTS



Active

PRODUCT DRAWING
English

See All Documentation

TE CONNECTIVITY
245W042-25-0
Raychem

245W042-25-0
TE Internal Number: CX4131-000

Always EU RoHS/ELV Compliant

Connector or Backshell Outside Diameter .787 in, 20 mm

Wire/Cable Outside Diameter .31 in, 8 mm

Molded Part Shape 45°

Lipped Yes

Operating Temperature Range(°C) -75 – 150
See All Features

North America

Contact us to request pricing, availability and customization options.

REQUEST ADDITIONAL INFORMATION



GET SAMPLE



SAVE TO LIST



CHECK FOR TOOLING



FIND SIMILAR PRODUCTS



DOCUMENTATIONFEATURES

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Shape 45°

Molded Part Type Molded Boot

Configuration Features

Lipped Yes

Body Features

Material Systems Code 25

Adhesive Pre-Coat No

Dimensions

Connector or Backshell Outside Diameter .787 in, 20 mm

Wire/Cable Outside Diameter .31 in, 8 mm

Usage Conditions

Operating Temperature Range(°C) -75 – 150

Operation/Application

Power Cable Accessory No

Industry Standards

Approved Standards MIS-34867

Other

Adhesive Options S1048 Separate Adhesive, -55°C to +105°C (-67°F to +221°F)

Adhesive Type Adhesive Purchased Separately

Product Compliance

Statement of Compliance
PDF

VIEW ALL PRODUCT COMPLIANCE

COMPATIBLE

No compatible products found for 245W042-25-0