

F-240-N



C^{RU} US
E101405

RoHS compliance

Screw

Quick Installation

Shock-resistant

Fuse tube fit

Ø6.4 × 30mm

Ø6.35 × 30mm

Ø6.35 × 31.8mm

Soldering heat condition


Specifications

Rating	250V-10A
Insulation resistance	DC500V, 100MΩ or more
Withstand voltage	AC2000V (1 minute)
Standard acquisition	C-UL Standard UL standards
Primary insulation (body)	Phenol (UL94V-0)
Primary insulation (insulator knob)	P.B.T. (UL94V-0)
Terminal fitting	187 tab terminal combined soldering (t0.5)
Body color	B (Black)
Mounting plate thickness	1.0 ~ 2.0mm
PRECAUTIONS	① If you have a standard product, please check the specifications and constraints.

Ordering Part F-240-N
Number

Order F-240-N
Example

Dimensions



Unit: mm

Last Updated: 2008/09/12

[Site Map](#)
[About this site](#)
[Terms and Conditions](#)

E-Mail: marketing@satoparts.co.jp Customer service representative ☎ 0120-70-7215
 Copyright (c) 2001-2010 SATO PARTS CO., LTD. All Rights Reserved.