


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.





RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/8/11	D.GRIFFIN
B	ECN5990: 2 MOUNTING SCREWS WERE 1 PACKAGE OF SCREWS	02/22/12	DFP
C	ECN6435: ADDED ROHS STAMP	09/28/12	DFP
D	ECN 6492: CHANGED NOTE TO "TDG1026KCS-R5E" WITHOUT PKG. UPD LOGO	10/29/12	D. DESJARDIN




2X #4-40 UNC-2B THRU

RECOMMENDED
PANEL OPENING



CAT 5E RIGHT ANGLE RJ45
SHIELDED COUPLER
(L-COM P/N TDG1026KCS-R5E
WITHOUT PACKAGING)

FLANGE MOUNTED KEYSTONE ADAPTOR



KIT SHOWN FULLY ASSEMBLED FOR CLARITY
(KIT IS SHIPPED UN-ASSEMBLED)


KIT INCLUDES:
1- COUPLER
1- FLANGE ADAPTOR
2- #4-40 x 1/4" MOUNTING SCREWS

NOTES:

MATERIAL:
FLANGED ADAPTOR: ZINC ALLOY
HARDWARE: STAINLESS STEEL

FINISH:
FLANGED ADAPTOR: NICKEL PLATE

KIT IS PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D. PARHAM	12/07/2011			CATEGORY TELECOM/MODULAR	
	CHECKED BY D. FRISIELLO	12/07/2011				
	APPROVED BY D. GALLAGHER	12/07/2011				
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION CPLR RJ45 F-F CAT5E SHIELDED RA			
			SIZE A	FSCM NO. 43321	DWG. NO. ECF504-SR5E	REV. D
			SCALE: NONE		CAD FILE: ECF504-SR5E.SLDDRW	
			SHEET 1 OF 1			