

Part Number : [936030090](#)

Product Description : Heavy-Duty Connector Kit, 24 Pole, Series S-E Female-Male Inserts, M25 Metal Cable Gland, M25 Die-cast Aluminum Hood-Side Entry, Bulkhead Mount Housing-Vertical, 2 Lever, Size 24B «104x27», Grey

Series Number : 93603

Status : Active

Product Category : Heavy-Duty Connectors

Engineering Part Number : 7924.7752.5



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93603
Description	Heavy-Duty Connector Kit, 24 Pole, Series S-E Female-Male Inserts, M25 Metal Cable Gland, M25 Die-cast Aluminum Hood-Side Entry, Bulkhead Mount Housing-Vertical, 2 Lever, Size 24B «104x27», Grey
Component Type	Connector Kit - Female+Male
Insert Series	S-E
Kit Component Parts	Heavy-Duty Metal Cable Gland, with Washer and Gaskets, M25x1.5 Thread, Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 24B «104x27», Extended M25 Thread, Grey, Heavy-Duty Screw Terminal Insert, Male, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27», Heavy-Duty Screw Terminal Insert, Female, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27», Heavy-Duty Standard (STD) Double Lever Bulkhead Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 24B «104x27», Grey
Product Name	Heavy-Duty Connectors

UPC	887191865560
-----	--------------

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	500V

Physical

Color - Cable Jacket	N/A
Component Size	24B «104X27»
Lock to Mating Part	Yes
Mounting Style	Bulkhead
Net Weight	605.000/g
Packaging Type	Bag
Thread Size	M25
Thread Type	(M) Metric

Kit Component Parts

Description	Part Number
Heavy-Duty Metal Cable Gland, with Washer and Gaskets, M25x1.5 Thread	<u>936000047</u>
Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 24B «104x27», Extended M25 Thread, Grey	<u>936013770</u>
Heavy-Duty Screw Terminal Insert, Male, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27»	<u>936010307</u>
Heavy-Duty Screw Terminal Insert, Female, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27»	<u>936010297</u>
Heavy-Duty Standard (STD)	<u>936013538</u>

Double Lever Bulkhead Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 24B «104x27», Grey	
--	--

This document was generated on Aug 29, 2026