


Miniature Tact Switches for SMT




Specifications:

Contact rating:	12 V DC, 50 mA
Contact resistance:	< 100 mΩ
Insulation resistance:	> 100 MΩ
Dielectric strength:	250 V AC (50 Hz or 60 Hz) for 1 minute
Operating temperature:	−40 °C to +85 °C
Operating force:	center: 3.6 N ± 0.6 N; 4 directions: 1.6 N ± 0.5 N
Mechanical life:	minimum 100 000 cycles
Material:	Cover: nickel plated Stem: high-temp. LCP Contact: stainless steel Terminal: phosphor bronze, silver-plated Base: high-temp. LCP, black
Packing:	850 pcs/reel

Models:

TSSJ 5



TSSJ 5-J

