



SILI-S 50



Item number 61.7617-*

Highly flexible stranded wire 50 mm² with reinforced insulation.

Technical data	
Rated Values	AC 1000 V, 200 A / DC 1500 V, 200 A
Standard color(s) *	
Lead insulation	SIL
Temperature range	-50 °C ... +90 °C
Strand design (n x Ø mm)	13024 x 0,07
Lead weighth	570.0 kg/km
Conductor diameter	10.5 mm
Cable diameter	14.9 mm
Insulation thickness	2.5 mm
Approvals	UR, CE, UKCA, EAC