

MATERIAL AND FINISH:

Insulator: Polycarbonate, UL-94V-0 rated
Contacts: IEC C13, 70°C; Brass
IEC C15, 120°C; Bronze

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A
Voltage rating: 250 VAC

ORDERING CODE:

43R01- 1 1 2



1) ELECTRICAL CIRCUIT
CONFIGURATION

1 = IEC C13, 10A 250V 70°C
A DIN 49 457

2 = IEC C15, 10A 250V 120°C
D DIN 49 458


2) COLOR

1 = BLACK
2 = GRAY



NOTES:

1. Contains integral cable clamp strain relief & internal screw type connections. Maximum wire gauge is 16AWG stranded.
2. Recommended screw torque: 1.2Nm
3. Recommended strip length for jacket and conductors:



RoHS
COMPLIANT

REVISIONS				Power Dynamics, Inc.			
REV	DATE	CHANGE	CHNG CHCK APPR	TOLERANCE UNLESS OTHERWISE SPECIFIED		Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076	
B	6/9/10	ADD C15 CONTACT MATERIAL	PB	DRAWN	GQ	DATE:	08/20/01
A	1/25/07	ADD NOTES 2 & 3: RoHS	PB	CHECK	TD	DATE:	08/22/01
				APPR	PB	DATE:	08/22/01
				PART: IEC 60320 C13 & C15 FEMALE POWER CORD PLUG, R/A LEFT HANDED CONNECTION		PART #: 43R01-X1X1	
				SIZE: A		SHEET 1 of 1	
				SCALE: NTS		ALL DIMENSIONS FOR REFERENCE ONLY DIMENSIONS ARE IN MILLIMETERS	
						REV: B	