


ZETTLER MAGNETICS CO., LTD.

3W AC-DC POWER MODULE SINGLE OUTPUT SERIES (P-S ISOLATED)


FEATURES

- Input Range 100-240VAC 50/60Hz
- Output range from 3.3V-24VDC
Also can be customized
- Switching Power Module For PCB Mount
- Encapsulated Design Prevent dust and humidity
- Self-Extinguishing Plastic 94V-0
- High efficiency, Low Temperature Rise
- Dielectric Strength 3600VAC
- Integrated perfect Protection
Low standby power and Leakage Current
- Integrated EMC network
- Dielectric Strength: 3600Vac 5mA1min
- Protection: OLP: Output over load protection
OSP: Output short protection
OTP: Over temperature protection
- Compact Size
- UL, TUV Approved


OUTLINE DIMENSIONS



P-S ISOLATED



Bottom View



ELECTRONIC SPECIFICATIONS

Order Number	Leakage Current (Ma)	No load Loss (W)	Output Voltage (VDC.)	Output Current (Ma)	Voltage Accuracy	Ripple	Noise	Ambient TEMP(°C)	Weight	Certificate		
										TUV	UL	CE
ZP03S0500WE	0.1mA	0.3W	5V	600	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S0600WE	0.1mA	0.3W	6V	500	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S0700WE	0.1mA	0.3W	7.5V	400	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S0800WE	0.1mA	0.3W	8V	375	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S0900WE	0.1mA	0.3W	9V	333	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S1000WE	0.1mA	0.3W	10V	300	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S1200WE	0.1mA	0.3W	12V	250	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S1500WE	0.1mA	0.3W	15V	200	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S1800WE	0.1mA	0.3W	18V	166	±5%	<50mV	<5% Vout	50	20g		●	
ZP03S2400WE	0.1mA	0.3W	24V	125	±5%	<50mV	<5% Vout	50	20g		●	