

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)
- M12 (B)
- M12 (D)
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (X)
- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



M12D-04BFFA-SL8001

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Metal, Non-shielded
Jacket Material: N/A
Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type Search

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

Specifications	Download / CAD
Nominal Current 4A	Connector Type Field Installable
Shielded Metal, Non-shielded	No. of Contacts 04
Connector Gender Female	Backshell Straight
Mating Style Screw Thread	IP Rating IP68
Assembly Style Solder	
More Options	

People Also Bought

